

## Microvalves Ø 4 and manual operating devices Microvalves Ø 4, 3/2 normally open and normally closed

Standard executions			
Version	Symbol	Code	Item
Normally open	2	030251	AM04132A
Normally closed	3 1	030252	AM04132C
Normally open with side connections	2	030253	AM04132AL
Normally closed with side connections	2 3 1	030254	AM04132CL







Series of poppet microvalves arranged for operating manually. Connections with integral 4 mm push-in fittings. According to the application you can choose between the version with bottom connections or with side ones.

For the choice of the operating device

see page 2.265.1.





Technical data			
Fluid	Compressed filtered air with or without lubrication. Lubrication, if started, must be continued.		
Pressure range	0 ÷ 8 bar		
Temperature range	-20 °C ÷ + 80 °C		
Operating force	5 N		
Flow	80 NI/min.		
Connections	With integral 4 mm push-in fittings		
Fixing	Through 2 holes (Ø 4 mm) on the body		
	Through 1 hole (Ø 22 mm) on panel (with operating device mounted)		
Mounting	In any position		
Materials	Body: Acetal resin Seals: Nitrile rubber (NBR)		